#### DELTA ELECTRONICS, INC. 252, SHANG YING ROAD, KUEI SAN TAOYUAN HSIEN 333, TAIWAN, R. O. C.

TEL : 886-(0)3-3591968 FAX : 886-(0)3-3591991

## SPECIFICATION FOR APPROVAL

Customer:		
Description:	DC FAN	
Customer P/N:		<u>REV:</u>
Delta Model NO.:	GFB0412EHS-F00	
Sample Rev:	00	Issue NO:
Sample Issue Date:	NOV.07.2003.	Quantity:

#### 1. SCOPE:

THIS SPECIFICATION DEFINES THE ELECTRICAL AND MECHANICAL CHARACTERISTICS OF THE DC BRUSHLESS AXIAL FLOW FAN. THE FAN MOTOR IS WITH TWO PHASES AND EIGHT POLES.

#### 2. CHARACTERS:

ITEM	DESCRIPTION			
RATED VOLTAGE	12 VDC			
OPERATION VOLTAGE	7.0 - 13.6 VDC			
INPUT CURRENT	1.25 (MAX. 1.50) A			
INPUT POWER	15.00(MAX. 18.00) W			
SPEED	front 15000/rear 11200 R.P.M. (ref.)			
MAX. AIR FLOW (AT ZERO STATIC PRESSURE)	0.770(MIN. 0.690) M <sup>3</sup> /MIN. 27.30 (MIN. 24.75 ) CFM			
MAX. AIR PRESSURE (AT ZERO AIRFLOW)	41.33(MIN. 37.27) mmH <sub>2</sub> 0 1.63 (MIN. 1.47 ) inchH <sub>2</sub> 0			
ACOUSTICAL NOISE (AVG.)	59.5 ( MAX. 63.5 ) dB-A			
INSULATION TYPE	 			


(continued)

DELTA MODEL: GFB0412EHS-F00

10 MEG OHM MIN. AT 500 VDC (BETWEEN FRAME AND (+) TERMINAL)
5 mA MAX. AT 500 VAC 60 Hz ONE MINUTE, (BETWEEN FRAME AND (+) TERMINAL)
OPEN TYPE
HOURS CONTINUOUS OPERATION AT 40 °C WITH 15 ~ 65 %RH.
TWO FANS ROTATE IN COUNTER DIRECTIONS SHOWED IN THE NAME PLATE SIDE
THE CURRENT WILL SHUT DOWN WHEN LOCKING ROTOR.
UL 1061 -F- AWG #24 BLACK WIRE NEGATIVE(-) RED WIRE POSITIVE(+) BLUE WIRE FREQUENCY(-F00)

NOTES: 1. ALL READINGS ARE MEASURED AFTER STABLY WARMING UP THROUGH 10 MINUTES.

- 2. THE VALUES WRITTEN IN PARENS, (), ARE LIMITED SPEC.
- 3. THE CHARACTERS SHOWED IN PAGE 1 IS THE CONDITION OF BOTH FANS RUN.
- 4. ACOUSTICAL NOISE MEASURING CONDITION:



NOISE IS MEASURED AT RATED VOLTAGE IN FREE AIR IN ANECHOIC CHAMBER WITH B & K SOUND LEVEL METER WITH MICROPHONE AT A DISTANCE OF ONE METER FROM THE FAN INTAKE.

page: 2

A00

PART NO:		 	
DELTA MODEL:	GFB0412EHS-F00	 	

**3. MECHANICAL:** 

-

3-1.	DIMENSIONS SI	EE I	DIMENSIO	NS D	RAWING
3–2.	FRAME		PLASTIC	UL:	94V-0
3–3.	IMPELLER		PLASTIC	UL:	94V-0
3-4.	BEARING SYSTEM		TWO BAI	T BE	ARINGS
3-5.	WEIGHT			80	GRAMS

#### 4. ENVIRONMENTAL:

4-1.	OPERATING TEMPERATURE	-10	TO	+6	<b>50</b> 1	DEGI	REE	C
4-2.	STORAGE TEMPERATURE	-40	<b>T</b> 0	+7	<b>'</b> 5 ]	DEGI	REE	C
4-3.	OPERATING HUMIDITY			5	TO	90	%	RH
4-4.	STORAGE HUMIDITY			5	TO	95	%	RH

#### 5. PROTECTION:

5-1. LOCKED ROTOR PROTECTION

IMPEDANCE OF MOTOR WINDING PROTECTS MOTOR FROM FIRE IN 96 HOURS OF LOCKED ROTOR CONDITION AT THE RATED VOLTAGE.

5-2. POLARITY PROTECTION

BE CAPABLE OF WITHSTANDING IF REVERSE CONNECTION FOR POSITIVE AND NEGATIVE LEADS.

6. RE OZONE DEPLETING SUBSTANCES:

6-1. NO CONTAINING PBEs, PBEOs, CFCs, PBBEs, PEDPEs AND HCFCs.


7. PRODUCTION LOCATION

-

7-1. PRODUCTS WILL BE PRODUCED IN CHINA OR THAILAND OR TAIWAN.

# DELTA MODEL: GFB0412EHS-F00

B.P & Q CURVE:



page: 4


A00

DELTA	MODEL:	GFB0412EHS-F00


#### 9. DIMENSION DRAWING:

LABEL:





\_\_\_\_\_






DELTA MODEL: GFB0412EHS-F00

FREQUENCY GENERATOR (FG) SIGNAL:


1. OUTPUT CIRCUIT - OPEN COLLECTOR MODE:



- CAUTION: THE RD SINGAL LEAD WIRE MUST BE KEPT AWAY FROM "+" LEAD WIRE & "-" LEAD WIRE.
- 2. SPECIFICATION:

 $\begin{array}{rcl} V_{\text{rc}} = & 15.0 \text{V} & \text{MAX.} & \text{Ic} = & 5 \text{mA} & \text{MAX.} \\ V_{\text{ce}} = & 0.5 \text{V} & \text{MAX.} & \text{R} & \geq & V_{\text{rc}} \ / \text{Ic} \end{array}$ 

3. FREQUENCY GENERATOR WAVEFORM:



### **Descriptions:**

- 1. Delta will not guarantee the performance of the products if the application condition falls outside the parameters set forth in the specification.
- 2. A written request should be submitted to Delta prior to approval if deviation from this specification is required.
- 3. Please exercise caution when handling fans. Damage may be caused when pressure is applied to the impeller, if the fans are handled by the lead wires, or if the fans are hard-dropped to the production floor.
- 4. Except as pertains to some special designs, there is no guarantee that the products will be free from any such safety problems or failures as caused by the introduction of powder, droplets of water or encroachment of insect into the hub.
- 5. The above-mentioned conditions are representative of some unique examples and viewed as the first point of reference prior to all other information.
- 6. It is very important to establish the correct polarity before connecting the fan to the power source. Positive (+) and Negative (-). Damage may be caused to the fans if connection is with reverse polarity, as there is no foolproof method to protect against such error.
- 7. Delta fans are not suitable where any corrosive fluids are introduced to their environment.
- 8. Please ensure all fans are stored according to the storage temperature limits specified. Do not store fans in a high humidity environment. We highly recommend performance testing is conducted before shipping, if the fans have been stored over 6 months.
- 9. Not all fans are provided with the Lock Rotor Protection feature. If you impair the rotation of the impeller for the fans that do not have this function, the performance of those fans will lead to failure.
- 10.Please be cautious when mounting the fan. Incorrect mounting of fans may cause excess resonance, vibration and subsequent noise.
- 11.It is important to consider safety when testing the fans. A suitable fan guard should be fitted to the fan to guard against any potential for personal injury.
- 12.Except where specifically stated, all tests are carried out at relative (ambient) temperature and humidity conditions of 25°C, 65%. The test value is only for fan performance itself.
- 13.Be certain to connect an "over  $4.7\mu$ F" capacitor to the fan externally when the application calls for using multiple fans in parallel, to avoid any unstable power.